



Cordless jigsaw, Type: 71360561



Order data

Order number	078210 71360561
GTIN	4014586900315
Item class	03F

Description

Version:

Sturdy general-purpose jigsaws with metal gearbox casings and overload protection. Cordless jigsaw, for metal and wood. Optimal control due to slim straight handle for precise cuts. The speed and orbital stroke are adjustable.

Note:

Suitable spare batteries and chargers can be found under No. 073808 – 073840.

Technical description

Weight	2.1 kg
Power supply	Mains operated
maximum sawn thickness steel	12 mm
Mitre angle adjustment	yes
tool change without tools	yes
Special features	Small handle circumference
Orbital stroke	4-fold

Format	Straight handle
maximum sawn thickness wood	150 mm
Manufacturer's designation	F-IRON Jig 26 AS
maximum vibration to EN	8.1 m/s ²
Rate of strokes	700 - 3000 min ⁻¹
Battery voltage	18 V
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
suitable battery - supplier / battery type / voltage	Bosch 18 V
Packaging	Modular case (L-Boxx)
Type of product	Saw