



Cordless circular saw, Type: 71360461



Order data

Order number	078209 71360461
GTIN	4014586900131
Item class	03F

Description

Version:

Compact cordless hand-held metal circular saw for fast, precise cold cutting of sheet metal, pipes and profiles up to a cutting depth of 57 mm.

- **Manual speed adjustment.**
- **Large chip catcher.**
- **Dead man's switch, restart protection and temperature shutdown.**

Supplied with:

Supplied with portable circular saw blade, chip catcher and L-BOXX. Without battery and charger.

Note:

See from No. 073814 and No. 073839 for suitable spare batteries and starter kits.

See No. 073863 - 073867 for suitable starter sets.

Technical description

Weight	3.05 kg
maximum cutting depth 90°	57 mm
Saw blade Ø	150 mm
maximum speed	2800 min ⁻¹

Battery voltage	18 V
suitable battery - supplier / battery type / voltage	Bosch 18 V
Power supply	Mains operated
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	0
maximum vibration to EN	<2,5 m/s ²
Version	Circular metal saw
Manufacturer's designation	F-IRONCut57AS
Saw blade bore Ø	20 mm
Type of product	Saw