

Garant UNILINE

ESD-CLEANING Wall wheeled, Type: M**Order data**

Order number	972890 M
GTIN	4067263126126
Item class	9GD

Description**Version:**

Very sturdy double-walled column made from sheet metal, perforated panels that can be used on both sides □ 9×9 mm on a 37 mm grid for attaching perforated panel accessories and Easyfix hooks and holders. Sturdy base plate permits easy set up and movement. **Electrically conductive wheels** with 4 castors Ø 125 mm, 2 with parking brake.

Standard:

DIN EN 61340-5-1

Supplied with:

ESD UNI Wall mobile; ESD easyBin recycling collection bin No. 972910 size 25; ESD open storage bin No. 972321 size AB1 with Easyfix box holder; Easyfix toolholder 90°, 100 mm long; Easyfix toolholder double 45°, 100 mm long; Easyfix bottle/can holder with inner Ø of 90 mm.

Colour:

Similar to RAL 7035 light grey **ESD powder-coated. Not configurable.**

Technical description

Number of castors with parking brake	2
Wheel Ø	125 mm

Depth	750 mm
Height	2067 mm
Number of castors without parking brake	2
Weight	69 kg
Usable width	600 mm
Width	600 mm
Safe working load	75 kg
Series	Cleaning Wall
Hoffmann perforated panel grid interval	9×9 mm
electrostatic characteristic	EGB/ESD
Type of product	Cleaning station

Accessories

ESD open storage bin Type AB1	972321 AB1
ESD easyBin recycling collection bin Volume 25 l	972910 25