

Garant GRIDLINE

**ESD roller cabinet for drawers, 26×24G, Height mm / number of drawers:
685/0****Order data**

Order number	972447 685/0
GTIN	4067263124986
Item class	9GK

Description**Version:**

Tool cabinet **ESD conductive**, to DIN EN 61340-5-1. Roller cabinet in 30×28G with 2 each ball-bearing **conductive** fixed wheels and castors, Ø 125 mm, castors with parking brakes. With raised edge on 4 sides. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

To take drawers 26×24G No. 972455.

Colour:

Body and drawers light grey similar to RAL 7035 **ESD powder-coated**.

Note:

- **All plastic components (e.g. covering caps and handles) are non-ESD conductive.**
- **Grounding via wheels.**

Technical description

Height	685 mm
Grounding	Grounding via wheels
Casing open at the top	no

Number of castors with parking brake	2
Usable height	400 mm
Wheel Ø	125 mm
ESD security	yes
maximum load capacity	600 kg
Depth	700 mm
Number of fixed wheels without parking brake	2
with anti-roll lip	yes
non-ESD conductive components	All plastic parts
Width	750 mm
Weight	55 kg
Drawer body usable height	400 mm
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Product name attribute	26x24G
Type of product	Roller cabinet

Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------