

Garant GRIDLINE

**ESD roller cabinet for drawers, 26×24G, Height mm / number of drawers:
985/0****Order data**

Order number	972447 985/0
GTIN	4067263124993
Item class	9GK

Description**Version:**

Tool cabinet **ESD conductive**, to DIN EN 61340-5-1. Roller cabinet in 30×28G with 2 each ball-bearing **conductive** fixed wheels and castors, Ø 125 mm, castors with parking brakes. With raised edge on 4 sides. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

To take drawers 26×24G No. 972455.

Colour:

Body and drawers light grey similar to RAL 7035 **ESD powder-coated**.

Note:

- **All plastic components (e.g. covering caps and handles) are non-ESD conductive.**
- **Grounding via wheels.**

Technical description

ESD security	yes
Casing open at the top	no
Wheel Ø	125 mm

non-ESD conductive components	All plastic parts
Drawer body usable height	700 mm
maximum load capacity	600 kg
Height	985 mm
Width	750 mm
Grounding	Grounding via wheels
Weight	65 kg
Number of castors with parking brake	2
with anti-roll lip	yes
Usable height	700 mm
Number of fixed wheels without parking brake	2
Depth	700 mm
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Product name attribute	26x24G
Type of product	Roller cabinet

Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------