

Garant GRIDLINE

ESD tool cabinet casing for drawers, 26×24G, Height: 900mm**Order data**

Order number	972450 900
GTIN	4067263126225
Item class	9GK

Description**Version:**

Tool cabinet casing in 30×28G, **ESD-conductive** according to DIN EN 61340-5-1, suitable for drawers 26×24G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock. Suitable drawers can be found under No. 972453.

Includes ESD grounding cable.

Colour:

Light grey similar to RAL 7035, **ESD powder-coated.**

Note:

- **When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.**
- **All plastic components (e.g. covering caps and handles) are non-ESD conductive.**

Technical description

Width	750 mm
Electronic locking system can be retrofitted	yes
Weight	41 kg
ESD security	yes

non-ESD conductive components	All plastic parts
Depth	700 mm
Height	900 mm
Depth in G	28
Grounding	Grounding point on the housing
maximum load capacity	4000 kg
Width in G	30
ESD grounding cable included	yes
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	26×24G
Type of product	Tool cabinet body

Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------