

Garant GRIDLINE

ESD tool cabinet casing for drawers, 26×24G, Height: 800mm**Order data**

Order number	972450 800
GTIN	4067263126263
Item class	9GK

Description**Version:**

Tool cabinet casing in 30×28G, **ESD-conductive** according to DIN EN 61340-5-1, suitable for drawers 26×24G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock. Suitable drawers can be found under No. 972453.

Includes ESD grounding cable.

Colour:

Light grey similar to RAL 7035, **ESD powder-coated.**

Note:

- **When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.**
- **All plastic components (e.g. covering caps and handles) are non-ESD conductive.**

Technical description

Height	800 mm
Width in G	30
Depth	700 mm
ESD grounding cable included	yes

Depth in G	28
ESD security	yes
non-ESD conductive components	All plastic parts
Electronic locking system can be retrofitted	yes
Weight	38 kg
Grounding	Grounding point on the housing
Width	750 mm
maximum load capacity	4000 kg
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	26×24G
Type of product	Tool cabinet body

Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------