

Garant GRIDLINE

ESD tool cabinet casing for drawers, 26×24G, Height: 1250mm**Order data**

Order number	972450 1250
GTIN	4067263126249
Item class	9GK

Description**Version:**

Tool cabinet casing in 30×28G, **ESD-conductive** according to DIN EN 61340-5-1, suitable for drawers 26×24G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock. Suitable drawers can be found under No. 972453.

Includes ESD grounding cable.

Colour:

Light grey similar to RAL 7035, **ESD powder-coated.**

Note:

- **When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.**
- **All plastic components (e.g. covering caps and handles) are non-ESD conductive.**

Technical description

Width	750 mm
Weight	50 kg
Depth in G	28
non-ESD conductive components	All plastic parts

Width in G	30
ESD grounding cable included	yes
maximum load capacity	4000 kg
Depth	700 mm
ESD security	yes
Electronic locking system can be retrofitted	yes
Height	1250 mm
Grounding	Grounding point on the housing
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	26×24G
Type of product	Tool cabinet body

Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------