

Garant GRIDLINE

## ESD tool cabinet casing for drawers, 26×24G, Height: 700mm



### Order data

Order number	972450 700
GTIN	4067263126270
Item class	9GK

### Description

#### Version:

Tool cabinet casing in 30×28G, **ESD-conductive** according to DIN EN 61340-5-1, suitable for drawers 26×24G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock. Suitable drawers can be found under No. 972453.

**Includes ESD grounding cable.**

#### Colour:

Light grey similar to RAL 7035, **ESD powder-coated.**

#### Note:

- **When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.**
- **All plastic components (e.g. covering caps and handles) are non-ESD conductive.**

### Technical description

Depth	700 mm
Width	750 mm
Electronic locking system can be retrofitted	yes
ESD security	yes

ESD grounding cable included	yes
Grounding	Grounding point on the housing
Width in G	30
Weight	35 kg
Depth in G	28
Height	700 mm
maximum load capacity	4000 kg
non-ESD conductive components	All plastic parts
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	26×24G
Type of product	Tool cabinet body

---

## Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------