

Garant GRIDLINE

**ESD tool cabinet casing for drawers, 26×24G, Height: 1500mm****Order data**

Order number	972450 1500
GTIN	4067263126256
Item class	9GK

**Description****Version:**

Tool cabinet casing in 30×28G, **ESD-conductive** according to DIN EN 61340-5-1, suitable for drawers 26×24G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock. Suitable drawers can be found under No. 972453.

**Includes ESD grounding cable.**

**Colour:**

Light grey similar to RAL 7035, **ESD powder-coated.**

**Note:**

- **When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.**
- **All plastic components (e.g. covering caps and handles) are non-ESD conductive.**

**Technical description**

Height	1500 mm
Depth in G	28
ESD grounding cable included	yes
Electronic locking system can be retrofitted	yes

Grounding	Grounding point on the housing
Depth	700 mm
non-ESD conductive components	All plastic parts
maximum load capacity	4000 kg
Weight	57 kg
ESD security	yes
Width	750 mm
Width in G	30
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	26×24G
Type of product	Tool cabinet body

---

## Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------