

Garant GRIDLINE

**ESD drawer 50 kg, 26×24G, Drawer front height: 125mm****Order data**

Order number	972453 125
GTIN	4067263126317
Item class	9GK

**Description****Version:**

**100% full extension drawers** with differential runners. Drawers with slots at 25-mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 50 kg.

**Supplied with:**

Drawers each complete with 1 pair drawer runner rails.

**Colour:**

Light grey similar to RAL 7035, **ESD powder-coated.**

**Technical description**

Application range	Tool cabinet
Usable depth	600 mm
Usable depth in G	24
Drawer usable area in G	26×24
Usable height	100 mm
Weight	15 kg
Usable width	650 mm
Usable width in G	26
Front height	125 mm

Drawer/pull-out shelf load capacity	50 kg
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	26×24G
Type of product	Drawer