

Garant GRIDLINE

**ESD drawer with one-hand individual drawer release system 50 kg, 26×24G,  
Drawer front height: 50mm****Order data**

Order number	972455 50
GTIN	4067263126348
Item class	9GK

**Description****Version:**

**100% full extension drawers** with differential runners. Drawers with slots at 25-mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 50 kg.

With **one-hand individual drawer release system** – prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

**Supplied with:**

Drawers each complete with 1 pair drawer runner rails.

**Colour:**

Light grey similar to RAL 7035, **ESD powder-coated**.

**Technical description**

Drawer/pull-out shelf load capacity	50 kg
Usable width	650 mm
with individual drawer release system	yes
Front height	50 mm
Individual drawer release system	One-hand
Usable width in G	26
Usable depth in G	24
Application range	Tool cabinet

Weight	11 kg
Drawer usable area in G	26×24
Usable height	25 mm
Usable depth	600 mm
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	26×24G
Type of product	Drawer