

Garant GRIDLINE

ESD drawer, 36×24G, Drawer front height: 100mm**Order data**

Order number	972473 100
GTIN	4067263126423
Item class	9GK

Description**Version:**

100% full extension drawers with differential runners.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 50 kg.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:

Drawer body and fronts light grey similar to RAL 7035 **ESD powder-coated**.

Technical description

Usable width	900 mm
Front height	100 mm
Drawer usable area in G	36×24
with individual drawer release system	no
Drawer/pull-out shelf load capacity	50 kg
Application range	Tool cabinet
Usable depth	600 mm
Usable depth in G	24
Usable width in G	36
Weight	18 kg

Usable height	75 mm
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	36×24G
Type of product	Drawer