

Garant GRIDLINE

**ESD drawer, 36×24G, Drawer front height: 50mm****Order data**

Order number	972473 50
GTIN	4067263126409
Item class	9GK

**Description****Version:**

**100% full extension drawers** with differential runners.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 50 kg.

**Supplied with:**

Drawers each complete with 1 pair drawer runner rails.

**Colour:**

Drawer body and fronts light grey similar to RAL 7035 **ESD powder-coated**.

**Technical description**

Usable depth	600 mm
Usable width in G	36
Usable depth in G	24
Drawer/pull-out shelf load capacity	50 kg
Usable width	900 mm
Weight	14 kg
with individual drawer release system	no
Application range	Tool cabinet
Front height	50 mm
Drawer usable area in G	36×24

Usable height	25 mm
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	36×24G
Type of product	Drawer