

Garant GRIDLINE

ESD tool cabinet casing for drawers, 36×24G, Height: 1000mm**Order data**

Order number	972470 1000
GTIN	4067263126508
Item class	9GK

Description**Version:**

ESD conductive tool cabinet casing in 40×28G, suitable for drawers 36×24G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock. Suitable drawers listed under No. 972473.

Includes ESD grounding cable.

Colour:

Body light grey similar to RAL 7035 **ESD powder-coated.**

Note:

All plastic components (e.g. covering caps) and handles are not ESD conductive. When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.

Technical description

Height	1000 mm
maximum load capacity	4000 kg
Number of pull-out shelves	0
Electronic locking system can be retrofitted	yes

ESD security	yes
Width in G	40
Number of drawers	0
Weight	50 kg
Depth	700 mm
Usable height	900 mm
Width	1000 mm
Grounding	Grounding point on the housing
Number of doors	0
ESD grounding cable included	yes
Depth in G	28
Usable height for drawers	900 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	36×24G
Type of product	Tool cabinet body

Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------