

Garant GRIDLINE

**ESD tool cabinet casing for drawers, 36×24G, Height: 900mm****Order data**

Order number	972470 900
GTIN	4067263126492
Item class	9GK

**Description****Version:**

ESD conductive tool cabinet casing in 40×28G, suitable for drawers 36×24G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock. Suitable drawers listed under No. 972473.

**Includes ESD grounding cable.**

**Colour:**

Body light grey similar to RAL 7035 **ESD powder-coated.**

**Note:**

All plastic components (e.g. covering caps) and handles are not ESD conductive. When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.

**Technical description**

ESD grounding cable included	yes
Depth	700 mm
Number of pull-out shelves	0
Number of doors	0
Number of drawers	0

Weight	48 kg
Width in G	40
Height	900 mm
Usable height	800 mm
Depth in G	28
Grounding	Grounding point on the housing
maximum load capacity	4000 kg
ESD security	yes
Electronic locking system can be retrofitted	yes
Usable height for drawers	800 mm
Width	1000 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	36×24G
Type of product	Tool cabinet body

---

## Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------