

Garant GRIDLINE

**ESD drawer, 36×24G, Drawer front height: 250mm****Order data**

Order number	972473 250
GTIN	4067263126461
Item class	9GK

**Description****Version:**

**100% full extension drawers** with differential runners.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 50 kg.

**Supplied with:**

Drawers each complete with 1 pair drawer runner rails.

**Colour:**

Drawer body and fronts light grey similar to RAL 7035 **ESD powder-coated**.

**Technical description**

Drawer/pull-out shelf load capacity	50 kg
Usable width	900 mm
Front height	250 mm
Weight	24 kg
Usable depth	600 mm
Drawer usable area in G	36×24
Usable width in G	36
with individual drawer release system	no
Application range	Tool cabinet

Usable depth in G	24
Usable height	225 mm
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	36×24G
Type of product	Drawer