

Garant GRIDLINE

ESD tool cabinet casing for drawers, 36×24G, Height: 800mm**Order data**

Order number	972470 800
GTIN	4067263126485
Item class	9GK

Description**Version:**

ESD conductive tool cabinet casing in 40×28G, suitable for drawers 36×24G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock. Suitable drawers listed under No. 972473.

Includes ESD grounding cable.

Colour:

Body light grey similar to RAL 7035 **ESD powder-coated.**

Note:

All plastic components (e.g. covering caps) and handles are not ESD conductive. When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.

Technical description

Usable height	700 mm
Depth	700 mm
Number of pull-out shelves	0
Width in G	40
Height	800 mm
Number of drawers	0
ESD grounding cable included	yes
Grounding	Grounding point on the housing
maximum load capacity	4000 kg
Weight	45 kg

Electronic locking system can be retrofitted	yes
Width	1000 mm
Depth in G	28
ESD security	yes
Number of doors	0
Usable height for drawers	700 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	36×24G
Type of product	Tool cabinet body

Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------