

Garant GRIDLINE

ESD tool cabinet casing for drawers, 36×24G, Height: 1500mm**Order data**

Order number	972470 1500
GTIN	4067263126522
Item class	9GK

Description**Version:**

ESD conductive tool cabinet casing in 40×28G, suitable for drawers 36×24G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock. Suitable drawers listed under No. 972473.

Includes ESD grounding cable.

Colour:

Body light grey similar to RAL 7035 **ESD powder-coated.**

Note:

All plastic components (e.g. covering caps) and handles are not ESD conductive. When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.

Technical description

Depth in G	28
Usable height for drawers	1400 mm
Usable height	1400 mm
Width in G	40

Number of pull-out shelves	0
maximum load capacity	4000 kg
Number of drawers	0
ESD security	yes
Weight	65 kg
Width	1000 mm
ESD grounding cable included	yes
Number of doors	0
Height	1500 mm
Electronic locking system can be retrofitted	yes
Grounding	Grounding point on the housing
Depth	700 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	36×24G
Type of product	Tool cabinet body

Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------