

Garant GRIDLINE

ESD tool cabinet complete with drawers 50 kg, 36×24G, Height mm / number of drawers: 1000/10



Order data

Order number	972460 1000/10
GTIN	4067263126553
Item class	9GK

Description

Version:

Tool cabinet **ESD conductive**, to DIN EN 61340-5-1. Completely equipped tool cabinet in 40×28G, with drawers 36×24G. Cabinet can be centrally locked by a cylinder lock. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25-mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Includes ESD grounding cable.

Colour:

Body and drawer body light grey similar to RAL 7035 **ESD powder-coated.**

Note:

- **When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.**
- **All plastic components (e.g. covering caps and handles) are non-ESD conductive.**

Technical description

Width	1000 mm
Weight	162 kg

Depth	700 mm
Usable height	900 mm
Height	1000 mm
Drawer usable area in G	36×24
Drawer usable depth in G	24
Drawer usable depth	600 mm
Drawer usable width in G	36
Drawer usable width	900 mm
Drawer/pull-out shelf load capacity	50 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Product name attribute	36×24G
Type of product	Tool cabinet

Accessories

Lock plate for GridLine Type HU21	914227 HU21
ESD tool cabinet casing for drawers Height 1000 mm	972470 1000
ESD drawer Drawer front height 100 mm	972473 100
ESD drawer Drawer front height 75 mm	972473 75