



## Carbide-tipped hammer drill set, Number of drills: 10



### Order data

|              |               |
|--------------|---------------|
| Order number | 789021 10     |
| GTIN         | 4058546414849 |
| Item class   | 76G           |

### Description

#### Version:

- **2 cutting edges. The 3 special Power Breaker projecting teeth of the MS2 generate micro-cracks in the material being drilled, these promote quicker advance by the drill and faster removal of material. The high quality carbide tip with particularly strong brazed joint guarantees long tool life, even in reinforced concrete. The reinforced core flutes (KVS) are vibration-damping, so the impact energy is transmitted directly to the drilling tip.**

PACKOUT-compatible plastic case.

#### Application:

For drilling concrete, natural stone, and masonry.

#### Content:

Hammer drill No. 789000: 1 pc. each size 5; 5; 6; 6 length 110 mm; size 6; 6; 8; 8; 10; 12 length 160 mm

### Technical description

|                                  |                 |
|----------------------------------|-----------------|
| Tool material                    | Carbide         |
| Use with impact / without impact | Impact drilling |

|                 |               |
|-----------------|---------------|
| Shank           | SDS Plus      |
| Type of product | Masonry drill |

---

## Accessories

|   |               |
|---|---------------|
| Carbide-tipped hammer drill SDS-plus Ø×overall length 10X160 mm | 789000 10X160 |
| Carbide-tipped hammer drill SDS-plus Ø×overall length 12X160 mm | 789000 12X160 |
| Carbide-tipped hammer drill SDS-plus Ø×overall length 5X110 mm  | 789000 5X110  |
| Carbide-tipped hammer drill SDS-plus Ø×overall length 6X110 mm  | 789000 6X110  |
| Carbide-tipped hammer drill SDS-plus Ø×overall length 6X160 mm  | 789000 6X160  |
| Carbide-tipped hammer drill SDS-plus Ø×overall length 8X160 mm  | 789000 8X160  |