

Carbide-tipped hammer drill set, Number of drills: 7



Order data

Order number	789021 7
GTIN	4058546414832
Item class	76G

Description

Version:

- **2 cutting edges. The 3 special Power Breaker projecting teeth of the MS2 generate micro-cracks in the material being drilled, these promote quicker advance by the drill and faster removal of material. The high quality carbide tip with particularly strong brazed joint guarantees long tool life, even in reinforced concrete. The reinforced core flutes (KVS) are vibration-damping, so the impact energy is transmitted directly to the drilling tip.**

PACKOUT-compatible plastic case.

Application:

For drilling concrete, natural stone, and masonry.

Content:

Hammer drill No. 789000: 1 pc. each size 5; 6 length 110 mm; size 5.5; 6; 8; 10; 12 length 160 mm

Technical description

Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill

Accessories

Carbide-tipped hammer drill SDS-plus Ø×overall length
6X110 mm

789000 6X110

Carbide-tipped hammer drill SDS-plus Ø×overall length
12X160 mm

789000 12X160