

 KOMET

KOMET KUB Quatron® indexable drill Combination shank, 2×D, Ø DC m7: 34mm

Order data

Order number	235500 34
GTIN	4047109026308
Item class	24P

Description
Version:
With combination shank.

- Optimised coolant channels for reliable chip evacuation.
- Point angle 174° for almost flat-bottomed holes.

Application:

- For stationary and rotating use.
- For difficult drilling conditions (rolling scale, sloping surfaces of castings, interrupted cutting).
- For bores with tolerance ± 0.2 mm.

With indexable inserts No. 236520 – 236576.

Supplied with:

Clamp screws (without indexable inserts).

Note:

Further sizes available on request.

Overhang L_A : 97 mm

Shank $\varnothing D_s$: 32 mm

Shank length L_s : 60 mm

ISO code indexable insert: SOEX 120508 44-..

Pack of insert screws: 239652 20IP (6.3 Nm)

Technical description

Number of cutting edges Z	1
Reach L_1	68 mm

Pack of insert screws	239652 20IP (6.3 Nm)
Shank $\varnothing D_s$	32 mm
ISO code indexable insert	SOEX 120508 44-..
Shank length L_s	60 mm
Series	KUB Quatron®
Nominal $\varnothing D$	34
Overall length L	157 mm
Overhang L_A	97 mm
Drill depth for indexable insert drill up to	2xD
Shank	DIN 6535 HE, DIN 6595
Use for drilling	Centre drilling
Use for drilling	limited cross-drilling
Use for drilling	oblique spot drilling
Use for drilling	Cross-drilling
Use for drilling	Centre drilling
Use for drilling	Aperture
Use for drilling	oblique exit
Use for drilling	convex
Through-coolant	yes
Type of product	Indexable drill

Accessories

PrecisionBit for Torx Plus®, shank E 6.3 Torx Plus® profile 20IP	674252 20IP
Torx Plus® insert screw set 10 pieces Drive 20IP	239652 20IP
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600

