



Roller cabinet incl. general-purpose tool set, 241 pieces for 7 drawers, Type: 1



Order data

Order number	689500 1
GTIN	4067263129516
Item class	66H

Description

Version:

Compact roller cabinet with 7 drawers. The drawers are equipped with a **241-piece HOLEX general-purpose tool set**, consisting of the following configuration: Spanners, pliers, 1/4-inch and 1/2-inch sockets, striking tools, circlip pliers, screwdrivers and supplementary articles. The tools in the upper **6 drawers** fit into precise, two-tone PE rigid foam inlays, in which each tool has its own defined place in the roller cabinet. The tools in the bottom drawer can be inserted loose and individually supplemented with additional tools.

Supplied with:

Roller cabinet with full extension and 7 drawers: 1× No. 914705 size 7
 Measuring tools and accessories – 22 pieces: 1 pc. No. 689501 size 1 rigid foam inlay
 1 pc. No. 081437 size BLACK LED torch, with batteries
 1 pc. No. 085154 size B permanent marker Dura-Ink® 15
 1 pc. No. 096845 size CLEAR comfort safety goggles
 1 pc. No. 410200 size 150 caliper, vernier 1/20
 1 pc. No. 458800 size HM straight carbide scriber
 1 pc. No. 461805 size 300 steel rule bendable, narrow, stainless, matt with graduations on rear
 1 pc. No. 462014 size 3 tape measure mm/inch reading
 1 pc. No. 466200 size 2 plastic folding rule
 1 pc. No. 467436 size 400 aluminium spirit level, with magnet
 1 pc. No. 844525 size 1F cable knife with plastic handle, folding
 1 pc. No. 845010 size 10 snap-off blade set, 10 pieces, 18 mm "experience"
 1 pc. No. 845039 size 160 universal knife with zinc die-cast handle, for 18 mm blades
 1 pc. No. 452600 size 150X100 try square, accuracy 2

Spanner set – 21 pieces: 1 pc. No. 689501 size 2 rigid foam inlay
1 pc. No. 613950 size 21; 22 combination spanner
1 pc. No. 613960 size 9 combination spanner set
1 pc. No. 614805 size 7; 8; 10; 13; 17 open-ended spanner / ratchet ring spanner
1 pc. No. 622201 size 7; 8; 10; 13 socket spanner with handle, long
1 pc. No. 813961 size 200 adjustable spanner with grip
Socket set 1/4 and 1/2 inch – 115 pieces: 1 pc. No. 689501 size 3 rigid foam inlay
1 pc. No. 631020 size 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 13 hexagon socket, 1/4 inch
1 pc. No. 631720 size 3; 4; 5 hexagon bit socket, 1/4 inch, short
1 pc. No. 632090 size 1/4 reversible ratchet, 1/4 inch with ejector
1 pc. No. 632420 size 50; 100 extension, 1/4 inch
1 pc. No. 633029 size 116 T-handle, 1/4 inch
1 pc. No. 633520 size 1/4 universal joint 1/4 inch
1 pc. No. 640190 size 1/2 reversible ratchet, 1/2 inch with ejector
1 pc. No. 641020 size 125; 255 extension, 1/2 inch
1 pc. No. 641320 size 295 T-handle, 1/2 inch
1 pc. No. 641620 size 1/2 universal joint, 1/2 inch
1 pc. No. 642120 size 13; 14; 15; 16; 17; 18; 19; 21; 22; 24 bi-hexagon socket, 1/2 inch
1 pc. No. 643220 size 5; 6; 8; 10; 12; 14; 17 hexagon bit socket 1/2 inch
1 pc. No. 675597 size 71 bit set, 71 pieces
1 pc. No. 676566 size 1 magnetic bitholding screwdriver with magazine with 1/4 inch bits, with ratchet and magnet
1 pc. No. 676668 size 60 screwdriver holder with magnet for 1/4 inch bits
1 pc. No. 676950 size 4/4 adapter with 1/4 inch C 6.3 hexagon shank
Screwdriver set – 32 pieces: 1 pc. No. 689501 size 4 rigid foam inlay
1 pc. No. 625701 size TX6; TX7; TX8; TX9; TX10; TX15; TX20; TX25 screwdriver for Torx®
1 pc. No. 627225 size 9 hexagon key L-wrench set, nickel-plated
1 pc. No. 660701 size 2.5; 3.5; 5.5; 7; 8; 10 screwdriver for slot-head, with power grip
1 pc. No. 664201 size 4; 5.5; 6.5 screwdriver for slot-head, short
1 pc. No. 668401 size 0; 1; 2; 3 screwdriver for Phillips, with power grip
1 pc. No. 668471 size 1; 2 screwdriver for Phillips, short
Pliers set – 12 pieces: 1 pc. No. 689501 size 5 rigid foam inlay
1 pc. No. 702995 size 180 vanadium combination pliers, bright finished, with two-component grips
1 pc. No. 706145 size 250 water pump pliers chemically blacked, with grips
1 pc. No. 713195 size 200 snipe nose pliers straight, bright finished, with grips
1 pc. No. 713595 size 200 snipe nose pliers angled, bright finished, with grips
1 pc. No. 719805 size J1; J2 internal circlip pliers, Form C, straight jaws
1 pc. No. 719905 size A1; A2 external circlip pliers, Form A, straight jaws
1 pc. No. 725245 size 160 side cutter, bright finished, with grips
1 pc. No. 818305 small pipe cutter with 4 guide rollers
1 pc. No. 860351 size 50 spring clamp
Abrasive media and striking tool assortment – 18 pieces: 1 pc. No. 689501 size 6 rigid foam inlay
1 pc. No. 517420 size 250 file set with 2-component handle, 5 pieces, in a tool roll

1 pc. No. 557660 size F universal abrasive cleaner
 1 pc. No. 575000 size 4 wire hand brush, steel wire smooth 0.35 mm
 1 pc. No. 748000 size 0.9; 1.4; 1.8; 2.4; 2.8; 3.4; 3.9; 4.9; 5.9 pin punch with guide sleeve
 1 pc. No. 750530 size 500 engineer's hammer with 3-component handle
 1 pc. No. 755500 size A400 rubber mallet black
 Supplementary articles – 21 pieces: 1 pc. No. 081670 size 500 magnetic retriever, flexible
 1 pc. No. 115051 size 1-10 HOLEX CleverDrill jobber drill set HSS No. 114031 in a case
 1 pc. No. 580800 size metal saw frame with handle, with bi-metal blade, 24 teeth
 1 pc. No. WM0002 size E playing cards "Schafskopf"

Note:

Tools are supplied loose. The equipped roller cabinet 689500 size 1 can be dispatched only to destinations within the EU.

Technical description

Number of drawers	7
Type of product	Roller cabinet

Accessories

LED torchwith batteries Colour BLACK	081437 BLACK
Magnetic retriever flexible Magnet tensile force 500 g	081670 500
Dura-Ink® 15 permanent marker Writing colour B	085154 B
Comfort safety glasses Lens tinting CLEAR	096845 CLEAR
HOLEX CleverDrill jobber drill set HSS No. 114031 in a case Type 1-10	115051 1-10
Vernier caliperVernier 1/20 Measuring range 150 mm	410200 150
Straight carbide scriber Type HM	458800 HM
Flexible steel rule narrow, stainlessmatt finished with graduations on rear Overall length 300 mm	461805 300
Tape measure with mm/inch graduations Tape length 3 m	462014 3
Plastic folding rule Length 2 m	466200 2
Aluminium spirit levelwith magnet Length 400 mm	467436 400
	517420 250

File set with 2-component handle, 5 pieces in a tool roll
Length without tang 250 mm

Universal abrasive cleaner Type F	557660 F
Wire hand brush Smooth steel wire 0.35 mm Number of rows of bristles 4	575000 4
Hacksaw frame with handle with bimetal blade 24 teeth	580800
Combination spanner Width across flats 21 mm	613950 21
Combination spanner Width across flats 22 mm	613950 22
Combination spanner set Number of keys 9	613960 9
Open ended spanner / ratchet ring spanner Width across flats 10 mm	614805 10
Open ended spanner / ratchet ring spanner Width across flats 13 mm	614805 13
Open ended spanner / ratchet ring spanner Width across flats 17 mm	614805 17
Open ended spanner / ratchet ring spanner Width across flats 7 mm	614805 7
Open ended spanner / ratchet ring spanner Width across flats 8 mm	614805 8
Nut spinner with handle long Width across flats 10 mm	622201 10
Nut spinner with handle long Width across flats 13 mm	622201 13
Nut spinner with handle long Width across flats 7 mm	622201 7
Nut spinner with handle long Width across flats 8 mm	622201 8
Screwdriver for Torx® Torx® profile TX10	625701 TX10
Screwdriver for Torx® Torx® profile TX15	625701 TX15
Screwdriver for Torx® Torx® profile TX20	625701 TX20
Screwdriver for Torx® Torx® profile TX25	625701 TX25
Screwdriver for Torx® Torx® profile TX6	625701 TX6
Screwdriver for Torx® Torx® profile TX7	625701 TX7
Screwdriver for Torx® Torx® profile TX8	625701 TX8
Screwdriver for Torx® Torx® profile TX9	625701 TX9
	627225 9

Hexagon key L-wrench setnickel-plated Number of screwdrivers 9

Hexagon socket, 1/4 inch Width across flats 10 mm	631020 10
Hexagon socket, 1/4 inch Width across flats 11 mm	631020 11
Hexagon socket, 1/4 inch Width across flats 13 mm	631020 13
Hexagon socket, 1/4 inch Width across flats 4 mm	631020 4
Hexagon socket, 1/4 inch Width across flats 4,5 mm	631020 4,5
Hexagon socket, 1/4 inch Width across flats 5 mm	631020 5
Hexagon socket, 1/4 inch Width across flats 5,5 mm	631020 5,5
Hexagon socket, 1/4 inch Width across flats 6 mm	631020 6
Hexagon socket, 1/4 inch Width across flats 7 mm	631020 7
Hexagon socket, 1/4 inch Width across flats 8 mm	631020 8
Hexagon socket, 1/4 inch Width across flats 9 mm	631020 9
Hexagon bit socket, 1/4 inchshort Hexagon 3 mm	631720 3
Hexagon bit socket, 1/4 inchshort Hexagon 4 mm	631720 4
Hexagon bit socket, 1/4 inchshort Hexagon 5 mm	631720 5
Reversible ratchet, 1/4 inch with ejector Type 1/4	632090 1/4
Extension, 1/4 inch overall length 100 mm	632420 100
Extension, 1/4 inch overall length 50 mm	632420 50
T-handle, 1/4 inch overall length 116 mm	633029 116
Universal joint 1/4 inch Type 1/4	633520 1/4
Reversible ratchet, 1/2 inch with ejector Type 1/2	640190 1/2
Extension, 1/2 inch overall length 125 mm	641020 125
Extension, 1/2 inch overall length 255 mm	641020 255
T-handle, 1/2 inch overall length 295 mm	641320 295
Universal joint, 1/2 inch Type 1/2	641620 1/2
Bi-hexagon socket, 1/2 inch Width across flats 13 mm	642120 13
Bi-hexagon socket, 1/2 inch Width across flats 14 mm	642120 14
Bi-hexagon socket, 1/2 inch Width across flats 15 mm	642120 15
Bi-hexagon socket, 1/2 inch Width across flats 16 mm	642120 16

Bi-hexagon socket, 1/2 inch Width across flats 17 mm	642120 17
Bi-hexagon socket, 1/2 inch Width across flats 18 mm	642120 18
Bi-hexagon socket, 1/2 inch Width across flats 19 mm	642120 19
Bi-hexagon socket, 1/2 inch Width across flats 21 mm	642120 21
Bi-hexagon socket, 1/2 inch Width across flats 22 mm	642120 22
Bi-hexagon socket, 1/2 inch Width across flats 24 mm	642120 24
Hexagon bit socket, 1/2 inch Hexagon 10 mm	643220 10
Hexagon bit socket, 1/2 inch Hexagon 12 mm	643220 12
Hexagon bit socket, 1/2 inch Hexagon 14 mm	643220 14
Hexagon bit socket, 1/2 inch Hexagon 17 mm	643220 17
Hexagon bit socket, 1/2 inch Hexagon 5 mm	643220 5
Hexagon bit socket, 1/2 inch Hexagon 6 mm	643220 6
Hexagon bit socket, 1/2 inch Hexagon 8 mm	643220 8
Screwdriver for slot-head, with power grip Blade width b 10 mm	660701 10
Screwdriver for slot-head, with power grip Blade width b 2,5 mm	660701 2,5
Screwdriver for slot-head, with power grip Blade width b 3,5 mm	660701 3,5
Screwdriver for slot-head, with power grip Blade width b 5,5 mm	660701 5,5
Screwdriver for slot-head, with power grip Blade width b 7 mm	660701 7
Screwdriver for slot-head, with power grip Blade width b 8 mm	660701 8
Screwdriver for slot-head, short Blade width b 4 mm	664201 4
Screwdriver for slot-head, short Blade width b 5,5 mm	664201 5,5
Screwdriver for slot-head, short Blade width b 6,5 mm	664201 6,5
Screwdriver for Phillips, with power grip Cross-head size 0	668401 0
Screwdriver for Phillips, with power grip Cross-head size 1	668401 1
Screwdriver for Phillips, with power grip Cross-head size 2	668401 2

Screwdriver for Phillips, with power grip Cross-head size 3	668401 3
Screwdriver for Phillips, short Cross-head size 1	668471 1
Screwdriver for Phillips, short Cross-head size 2	668471 2
Bit set 71 pieces Number of pieces 71	675597 71
Bit-holding screwdriver with magazine with 1/4 inch bits with ratchet and magnet Type 1	676566 1
Screwdriver holder for 1/4 inch bits with magnet Blade length 60 mm	676668 60
Adapter with 1/4 inch C 6.3 hexagon shank Type 4/4	676950 4/4
Vanadium combination pliers, bright finished, with two-component grips Overall length 180 mm	702995 180
Water pump pliers chemically blacked, with coated grips Overall length 250 mm	706145 250
Snipe-nose pliers, straight, bright finished, with grips Overall length 200 mm	713195 200
Snipe nose pliers, angled, bright finished, with grips Overall length 200 mm	713595 200
Circlip pliers Type J1	719805 J1
Circlip pliers Type J2	719805 J2
Circlip pliers Type A1	719905 A1
Circlip pliers Type A2	719905 A2
Side cutter, bright finish, with grips overall length 160 mm	725245 160
Pin punch with guide sleeve Tip Ø 0,9 mm	748000 0,9
Pin punch with guide sleeve Tip Ø 1,4 mm	748000 1,4
Pin punch with guide sleeve Tip Ø 1,8 mm	748000 1,8
Pin punch with guide sleeve Tip Ø 2,4 mm	748000 2,4
Pin punch with guide sleeve Tip Ø 2,8 mm	748000 2,8
Pin punch with guide sleeve Tip Ø 3,4 mm	748000 3,4
Pin punch with guide sleeve Tip Ø 3,9 mm	748000 3,9
Pin punch with guide sleeve Tip Ø 4,9 mm	748000 4,9
Pin punch with guide sleeve Tip Ø 5,9 mm	748000 5,9

Engineer's hammer with 3-component handle Weight without handle 500 g	750530 500
Black rubber hammer Type A400	755500 A400
Adjustable spanner with coated handle overall length 200 mm	813961 200
Small pipe cutter with 4 guide rollers	818305
Cable knife with plastic handle, folding Type 1F	844525 1F
Snap-off "experience" blades set, 10 pieces, 18 mm number 10	845010 10
General-purpose knife with zinc die-cast handle 18 mm overall length 160 mm	845039 160
Spring clamp Jaw capacity 50 mm	860351 50
Roller cabinet with full extension drawers Number of drawers 7	914705 7