



Roller cabinet incl. electrician's tool set, 111 pieces for 6 drawers, Type: 1



Order data

Order number	689505 1
GTIN	4067263129509
Item class	66H

Description

Version:

Compact roller cabinet with 7 drawers. The drawers are equipped with a **111-piece HOLEX electrician's tool set**, consisting of the following configuration: Spanners, pliers, 3/8 inch and 1/2 inch sockets, screwdrivers, supplementary articles and tools for stripping, cutting and crimping. The tools in the top **5 drawers** fit precisely in two-tone PE rigid foam inlays, in which each tool has its own defined place in the roller cabinet. The contents of the other 2 drawers can be individually selected.

Supplied with:

Roller cabinet with full extension and 7 drawers: 1× No. 914705 size 7
 Measuring tools and accessories – 22 pieces: 1 pc. No. 689506 size 1 rigid foam inlay
 1 pc. No. 085154 size B permanent marker Dura-Ink® 15
 1 pc. No. 096845 size CLEAR comfort safety goggles
 1 pc. No. 410200 size 150 caliper, vernier 1/20
 1 pc. No. 452600 size 150X100 try square, accuracy 2
 1 pc. No. 458800 size HM straight carbide scribe
 1 pc. No. 461805 size 300 steel rule bendable, narrow, stainless, matt with graduations on rear
 1 pc. No. 462014 size 3 tape measure mm/inch reading
 1 pc. No. 466200 size 2 plastic folding rule
 1 pc. No. 467475 size 250 control cabinet spirit level with magnet
 1 pc. No. 844525 size 1F cable knife with plastic handle, folding
 1 pc. No. 845010 size 10 snap-off blade set, 10 pieces, 18 mm "experience"
 1 pc. No. 845039 size 160 universal knife with zinc die-cast handle for 18 mm blades
 Spanner set – 22 pieces: 1 pc. No. 689506 size 2 rigid foam inlay

1 pc. No. 613333 size 8; 10; 11; 13; 14; 17; 19; 24 single open ended spanner, fully insulated
 1 pc. No. 614833 size 10; 11; 13; 14; 19; 24 single ended ratchet ring spanner, fully insulated
 1 pc. No. 618203 size 8; 10; 13; 14; 17; 19; 24 single ended ring spanner, fully insulated
 1 pc. No. 814006 size 200 adjustable spanner, insulated to VDE
 Socket set 1/8 and 3/2 inch – 35 pieces: 1 pc. No. 689506 size 3 rigid foam inlay
 1 pc. No. 637681 size 3/8 reversible ratchet, 3/8 inch with ejector, fully insulated
 1 pc. No. 637683 size 3/8 T-handle, 3/8 inch, fully insulated
 1 pc. No. 637685 size 125 extension, 3/8 inch, fully insulated
 1 pc. No. 637687 size 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19 hexagon socket, 3/8 inch, fully insulated
 1 pc. No. 637689 size 5; 6; 8 hexagon bit socket, 3/8 inch, fully insulated
 1 pc. No. 643801 size 1/2 reversible ratchet, 1/2 inch, fully insulated
 1 pc. No. 643803 size 1/2 T-handle, 1/2 inch, fully insulated
 1 pc. No. 643805 size 125 extension, 1/2 inch, fully insulated
 1 pc. No. 643807 size 10; 11; 12; 13; 14; 16; 17; 18; 19; 22; 24 hexagon socket, 1/2 inch, fully insulated
 1 pc. No. 643809 size 5; 6; 8; 10 hexagon bit socket, 1/2 inch, fully insulated
 Screwdriver set – 21 pieces: 1 pc. No. 689506 size 4 rigid foam inlay
 1 pc. No. 625780 size TX8; TX9; TX10; TX15; TX20; TX25; TX30 electrician's screwdriver for Torx®, fully insulated
 1 pc. No. 663301 size 2.5; 3; 3.5; 4; 5.5; 6.5; 8; 10 electrician's screwdriver for slot-head, fully insulated
 1 pc. No. 665050 size 3 single-pole phase tester
 1 pc. No. 668631 size 0; 1; 2; 3; 4 electrician's screwdriver for Phillips, fully insulated
 Supplementary articles – 2 pieces: 1 pc. No. 081670 size 500 magnetic retriever, flexible
 1 pc. No. 473320 size 9917 multimeter
 1 pc. No. WM0002 size E playing cards "Schafkopf"

Note:

Tools are supplied loose. The equipped roller cabinet 689505 size 1 can be dispatched only to destinations within the EU.

Technical description

Number of drawers	6
Type of product	Roller cabinet

Accessories

LED torchwith batteries Colour BLACK	081437 BLACK
--------------------------------------	--------------

Magnetic retriever flexible Magnet tensile force 500 g	081670 500
Dura-Ink® 15 permanent marker Writing colour B	085154 B
Comfort safety glasses Lens tinting CLEAR	096845 CLEAR
Vernier caliperVernier 1/20 Measuring range 150 mm	410200 150
Straight carbide scriber Type HM	458800 HM
Flexible steel rule narrow, stainlessmatt finished with graduations on rear Overall length 300 mm	461805 300
Tape measure with mm/inch graduations Tape length 3 m	462014 3
Plastic folding rule Length 2 m	466200 2
Control cabinet spirit levelwith magnet Length 250 mm	467475 250
Multimeter Device type 9917	473320 9917
Single open ended spannerfully insulated Width across flats 10 mm	613333 10
Single open ended spannerfully insulated Width across flats 11 mm	613333 11
Single open ended spannerfully insulated Width across flats 13 mm	613333 13
Single open ended spannerfully insulated Width across flats 14 mm	613333 14
Single open ended spannerfully insulated Width across flats 17 mm	613333 17
Single open ended spannerfully insulated Width across flats 19 mm	613333 19
Single open ended spannerfully insulated Width across flats 24 mm	613333 24
Single open ended spannerfully insulated Width across flats 8 mm	613333 8
Single ended ratchet ring spannerfully insulated Width across flats 10 mm	614833 10
Single ended ratchet ring spannerfully insulated Width across flats 11 mm	614833 11
Single ended ratchet ring spannerfully insulated Width across flats 13 mm	614833 13

Single ended ratchet ring spannerfully insulated Width across flats 14 mm	614833 14
Single ended ratchet ring spannerfully insulated Width across flats 19 mm	614833 19
Single ended ratchet ring spannerfully insulated Width across flats 24 mm	614833 24
Single ended ring spannerfully insulated Width across flats 10 mm	618203 10
Single ended ring spannerfully insulated Width across flats 13 mm	618203 13
Single ended ring spannerfully insulated Width across flats 14 mm	618203 14
Single ended ring spannerfully insulated Width across flats 17 mm	618203 17
Single ended ring spannerfully insulated Width across flats 19 mm	618203 19
Single ended ring spannerfully insulated Width across flats 24 mm	618203 24
Single ended ring spannerfully insulated Width across flats 8 mm	618203 8
Electrician's screwdriver for Torx®,fully insulated Torx® profile TX10	625780 TX10
Electrician's screwdriver for Torx®,fully insulated Torx® profile TX15	625780 TX15
Electrician's screwdriver for Torx®,fully insulated Torx® profile TX20	625780 TX20
Electrician's screwdriver for Torx®,fully insulated Torx® profile TX25	625780 TX25
Electrician's screwdriver for Torx®,fully insulated Torx® profile TX30	625780 TX30
Electrician's screwdriver for Torx®,fully insulated Torx® profile TX8	625780 TX8
Electrician's screwdriver for Torx®,fully insulated Torx® profile TX9	625780 TX9
	637681 3/8

Reversible ratchet, 3/8 inch, with ejectorfully insulated
Type 3/8

T-handle, 3/8 inchfully insulated Type 3/8	637683 3/8
Extension, 3/8 inchfully insulated overall length 125 mm	637685 125
Hexagon socket, 3/8 inchfully insulated Width across flats 10 mm	637687 10
Hexagon socket, 3/8 inchfully insulated Width across flats 11 mm	637687 11
Hexagon socket, 3/8 inchfully insulated Width across flats 12 mm	637687 12
Hexagon socket, 3/8 inchfully insulated Width across flats 13 mm	637687 13
Hexagon socket, 3/8 inchfully insulated Width across flats 14 mm	637687 14
Hexagon socket, 3/8 inchfully insulated Width across flats 15 mm	637687 15
Hexagon socket, 3/8 inchfully insulated Width across flats 16 mm	637687 16
Hexagon socket, 3/8 inchfully insulated Width across flats 17 mm	637687 17
Hexagon socket, 3/8 inchfully insulated Width across flats 18 mm	637687 18
Hexagon socket, 3/8 inchfully insulated Width across flats 19 mm	637687 19
Hexagon socket, 3/8 inchfully insulated Width across flats 8 mm	637687 8
Hexagon bit socket 3/8 inchfully insulated Hexagon 5 mm	637689 5
Hexagon bit socket 3/8 inchfully insulated Hexagon 6 mm	637689 6
Hexagon bit socket 3/8 inchfully insulated Hexagon 8 mm	637689 8
Reversible ratchet, 1/2 inchfully insulated Type 1/2	643801 1/2
T-handle, 1/2 inchfully insulated Type 1/2	643803 1/2
Extension, 1/2 inchfully insulated overall length 125 mm	643805 125
Hexagon socket, 1/2 inchfully insulated Width across flats 10 mm	643807 10

Hexagon socket, 1/2 inch fully insulated Width across flats 11 mm	643807 11
Hexagon socket, 1/2 inch fully insulated Width across flats 12 mm	643807 12
Hexagon socket, 1/2 inch fully insulated Width across flats 13 mm	643807 13
Hexagon socket, 1/2 inch fully insulated Width across flats 14 mm	643807 14
Hexagon socket, 1/2 inch fully insulated Width across flats 16 mm	643807 16
Hexagon socket, 1/2 inch fully insulated Width across flats 17 mm	643807 17
Hexagon socket, 1/2 inch fully insulated Width across flats 18 mm	643807 18
Hexagon socket, 1/2 inch fully insulated Width across flats 19 mm	643807 19
Hexagon socket, 1/2 inch fully insulated Width across flats 22 mm	643807 22
Hexagon socket, 1/2 inch fully insulated Width across flats 24 mm	643807 24
Hexagon bit socket, 1/2 inch fully insulated Hexagon 10 mm	643809 10
Hexagon bit socket, 1/2 inch fully insulated Hexagon 5 mm	643809 5
Hexagon bit socket, 1/2 inch fully insulated Hexagon 6 mm	643809 6
Hexagon bit socket, 1/2 inch fully insulated Hexagon 8 mm	643809 8
Electrician's screwdriver for slot-head fully insulated Blade width b 10 mm	663301 10
Electrician's screwdriver for slot-head fully insulated Blade width b 2,5 mm	663301 2,5
Electrician's screwdriver for slot-head fully insulated Blade width b 3 mm	663301 3
Electrician's screwdriver for slot-head fully insulated Blade width b 3,5 mm	663301 3,5
Electrician's screwdriver for slot-head fully insulated Blade width b 4 mm	663301 4

Electrician's screwdriver for slot-headfully insulated Blade width b 5,5 mm	663301 5,5
Electrician's screwdriver for slot-headfully insulated Blade width b 6,5 mm	663301 6,5
Electrician's screwdriver for slot-headfully insulated Blade width b 8 mm	663301 8
Single-pole phase tester Blade width 3 mm	665050 3
Electrician's screwdriver for Phillipsfully insulated Cross-head size 0	668631 0
Electrician's screwdriver for Phillipsfully insulated Cross-head size 1	668631 1
Electrician's screwdriver for Phillipsfully insulated Cross-head size 2	668631 2
Electrician's screwdriver for Phillipsfully insulated Cross-head size 3	668631 3
Electrician's screwdriver for Phillipsfully insulated Cross-head size 4	668631 4
Pliers set, 4 piecesVDE insulated Number of pliers 4	700121 4
Water pump pliersVDE grips overall length 250 mm	705746 250
Precision wire stripper, steplessly adjustable for wire Ø 016-08 mm	728501 016-08
Crimping tool for terminal sleeves for conductor cross-section 10 mm ²	729456 10
Small cable cutter overall length 160 mm	730100 160
Electrician's scissorswith 2-component grip and wire cutter overall length 140 mm	768802 140
Adjustable spannerVDE insulated overall length 200 mm	814006 200
Cable knife with plastic handle, folding Type 1F	844525 1F
Snap-off "experience" blades set, 10 pieces, 18 mm number 10	845010 10
General-purpose knife with zinc die-cast handle18 mm overall length 160 mm	845039 160
Roller cabinetwith full extension drawers Number of drawers 7	914705 7

