

Garant GRIDLINE

ESD casing 24G for individual configuration with drawers, 20×20G, Height of the housing: 800mm**Order data**

Order number	972040 800
GTIN	4067263129615
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **For 100% full extension drawers** with differential runners and 75 kg load capacity. Can be locked centrally with a cylinder lock.

Application:

Drawer casing for individual fitting of ESD workstation No. 972010 – 972015, ESD height-adjustable workstations No. 972017, ESD workbenches No. 972150 – 972195.

Colour:

Body light grey similar to RAL 7035 **ESD powder-coated**.

Note:

- **All plastic components (e.g. covering caps) and handles are not ESD conductive. When equipping the casing with drawers, check that the sum of the individual drawer front heights adds up to the usable casing height.**
- **Only one drawer with a front height of 50 mm is possible per casing, only in the uppermost position.**

Technical description

Width in G	24
------------	----

Height	800 mm
Width	600 mm
Drawer usable area in G	20×20
Usable height for drawers	700 mm
Depth	650 mm
Usable height	700 mm
Weight	21.6 kg
Depth in G	26
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Product name attribute	20×20G
Type of product	Workbench casing

Accessories

Lock plate for GridLine Type KO21	914227 KO21
-----------------------------------	-------------