

Garant GRIDLINE

ESD drawer, 20×20G, Drawer front height: 200mm



Order data

Order number	972045 200
GTIN	4067263129684
Item class	9GG

Description

Version:

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

Suitable for:

All ESD casings 24G.

Colour:

Drawer body and front light grey similar to RAL 7035 **ESD powder-coated.**

Note:

Only one drawer with a front height of 50 mm is possible per casing, only in the uppermost position.

Technical description

Drawer/pull-out shelf load capacity	75 kg
Front height	200 mm
Usable depth in G	20
Usable depth	500 mm
Usable width	500 mm
Drawer usable area in G	20×20
Usable height	175 mm

Data sheet

Usable width in G	20
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	20×20G
Type of product	Drawer