

Garant GRIDLINE

**ESD drawer, 20×20G, Drawer front height: 75mm****Order data**

Order number	972045 75
GTIN	4067263129646
Item class	9GG

**Description****Version:**

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

**Suitable for:**

All ESD casings 24G.

**Colour:**

Drawer body and front light grey similar to RAL 7035 **ESD powder-coated**.

**Note:**

Only one drawer with a front height of 50 mm is possible per casing, only in the uppermost position.

**Technical description**

Usable depth	500 mm
Usable width in G	20
Drawer usable area in G	20×20
Front height	75 mm
Drawer/pull-out shelf load capacity	75 kg
Usable width	500 mm
Usable depth in G	20
Usable height	50 mm
Drawer runner extension (partial/full extension)	100 %

## Data sheet

electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	20×20G
Type of product	Drawer