

Garant GRIDLINE

Storage shelf, Front height: 25mm**Order data**

Order number	935160 25
GTIN	4067263125785
Item class	9GK

Description**Version:**

Made of sheet metal with cross-bracing on the underside. Standard storage shelf for insertion.

Load capacity 150 kg.**Colour:**

Light grey RAL 7035, powder-coated.

Note:

- **The storage shelf also acts as the locking base in combination with the central locking No. 935590, 935595. Prepared for mounting cylinder locks in the fascia.**
- **25 mm high storage shelves cannot be combined with intermediate bridging rails and end rails.**

Technical description

Front height	25 mm
Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Storage shelf version	fixed shelf
Storage shelf version	straight shelf
Application range	Drawer/shelf combination unit
Material thickness	1.2 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Data sheet

Width	1453 mm
Depth	675 mm
Width in G	56
Depth in G	24
Type of product	Storage shelf