

Garant GRIDLINE

**Pull-out shelf 75 kg, 26×24G, Installation height: 75mm****Order data**

Order number	931184 75
GTIN	4067263126027
Item class	9GK

**Description****Version:**

Pull-out shelf with **100% full extension**. Open in front, shell height at sides 46 mm, installation height 75 mm. Without slots to take slotted dividers.

**Suitable for:**

Auxiliary cabinet 30×28G.

**Supplied with:**

Pull-out shelves each complete with 1 pair drawer runner rails.

**Colour:**

RAL 7035 light grey **powder-coated**.

**Note:**

Not suitable for fitting into mobile cabinets.

**Technical description**

Installation height	75 mm
Usable depth in G	24
Drawer usable area in G	26×24
Weight	13.8 kg
Application range	Tool cabinet
with individual drawer release system	no
Usable width in G	26
Material thickness	1.2 mm

Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×24G
Usable width	650 mm
Usable depth	600 mm
Type of product	Pull-out shelf