



## Kraftform Kompakt VDE sets, Number of pieces: 18



### Order data

Order number	667262 18
GTIN	4013288229991
Item class	63H

### Description

#### Version:

**Kraftform** handle with 154-mm-long **interchangeable blades (including control cabinet keys) fully insulated up to 1000 V** according to **DIN EN 6000 / VDE 0682-201** and a voltage tester (up to 250 V to VDE 0680/6) in a sturdy textile tool roll with hook and loop fastener and belt loop.

#### Advantage:

“Take it Easy” tool finder with colour marking by profiles – **to find the required tool quickly and easily.**

#### Content:

Slot-head blades: 0.4×2.5; 0.6×3.5; 0.8×4.0; 1.0×5.5

Blades for Phillips: PH1 and PH2

Pozidriv bits: PZ1 and PZ2

Phillips/slot-head blade (combination profile): PH/ S1 and PH/ S2 (combination profile)

Pozidriv/slot-head blade (combination profile): PZ/ S1 and PZ/ S2 (combination profile)

Square: 8 mm and 1/4 inch (89 mm long)

3-square: 9 mm (89 mm long)

Two-wing: (89 mm long)

Voltage tester No. 665030: Size 3

Kraftform handle for interchangeable blades No. 667411: Size 1

### Technical description

Number of pieces	18
Drive profile	Combination profile screwdriver Pozidriv / slot-head
Drive profile	Screwdriver for Phillips
Drive profile	Triangular sockets
Drive profile	Two-wing key
Drive profile	Slot-head screwdriver
Drive profile	Square sockets
Drive profile	Pozidriv screwdriver
Drive profile	Combination profile screwdriver Phillips / slot-head
Manufacturer's designation	KK VDE 18 Universal 1
Standard	DIN EN IEC 60900 / VDE 0682-201
Cap rotatable	no
Type of product	Screwdrivers

---

## Accessories

Single VDE Kraftform handle Type 1	667411 1
------------------------------------	----------