

**Garant****Screwdriver set, Number of pieces: 10****Order data**

Order number	667533 10
GTIN	4067263129929
Item class	61F

**Description****Version:**

Ergonomically shaped **power grip** with easy-grip **Haptoprene** surface and an impact-resistant plastic core. The special surface structure allows transmission of high torques, even with wet or oily hands.

**Double blade** of chromium vanadium special alloy combining maximum hardness and exceptional toughness.

Surface nickel-plated and chrome-plated. Black tips, accurately dimensioned.

**Content:**

2 slot-head blades: 0.8×4 mm / 0.6×3.5 mm; 1.2×6 mm / 1×5 mm

1 blade for Phillips: Size 1 / Size 2

1 blade for Pozidriv: Size 1 / Size 2

2 blades for Torx®: TX10 / TX15; TX20 / TX25

2 blades for hex: 2.5 / 3 mm; 4 / 5 mm

1 bit holder: 1 pc.

1 2-component handle: 1 pc.

**Supplied with:**

Textile roll-up wallet.

**Technical description**

Drive profile	Slot-head screwdriver
---------------	-----------------------

Drive profile	Screwdriver for Phillips
Drive profile	Pozidriv screwdriver
Drive profile	Hexagon screwdriver
Drive profile	Screwdriver for TORX® screws
Number of pieces	10
Material of handle	2-component Haptoprene
Cap rotatable	no
Ratchet function	no
Reamer bit included	no
Telescopic handle	no
Type of product	Screwdriver