

**Fabric adhesive tape UV-resistant, transparent, Width×length (mm× m):
48X20****Order data**

Order number	083618 48X20
GTIN	4063565106507
Item class	08M

Description**Version:**

tesa® Ultra Power Clear has been designed for use in indoor and outdoor areas. Thanks to its high UV and temperature resistance, it can also be used in extreme weather conditions and temperatures from -10°C to +90°C. The transparent repair tape is ideal for outdoor activities, but is of course also very useful in domestic households when performing (temporary) repairs.

Note:

The specified "best before" date for tesa® products is in relation to compliance with the specified storage guidelines.

Technical description

Length	20 m
Width	48 mm
Tensile strength	3.5 N/mm
Manufacturer's designation	4665
temperature-resistant up to	-10 - 90 °C

Storage temperature	15 - 35 °C
Adhesive strength on steel	0.9 N/mm
Adhesive	Synthetic rubber
Type of adhesive tape	single-sided
Colour	transparent
Storage humidity	50 - 70 %
Backing material	PE film
Fabric fineness	30 mesh
Stretch capability	27 %
Liner present	no
Thickness	0.17 mm
Product name attribute	transparent
Type of product	Adhesive tape