



KOMET® micro-adjustable drilling head B301, Ø Dmin: 29,5mm



Order data

Order number	238301 29,5
GTIN	4047109005655
Item class	24B

Description

Version:

With ABS® connection B301 and accepts M302 precision turning cartridge.

The smallest adjustment is 0.002 mm on the Ø using the vernier. Central coolant supply to the cutting edge.

Application:

For bores from Ø 29.5 to 121 mm.

For high precision setting, turning cartridge can be adjusted after clamping.

Note:

Please order the suitable precision cartridge No. 238310 (M302) and indexable inserts separately.

Technical description

Application	238310 10
ABS® shank Ø D _s	25
Minimum Ø D _{min}	29,5
Overhang L ₁	50 mm
Insert screw set	249900 SW3
Boring range Ø	29.5 - 36 mm
Shank	ABS
Use for drilling	Cross-drilling

Use for drilling	oblique exit
Use for drilling	oblique spot drilling
Through-coolant	yes
Type of product	Boring tool

Accessories

KOMET® precision cartridgeM302 Type 10	238310 10
--	-----------