


KOMET® precision cartridge M302, Type: 60

Order data

Order number	238310 60
GTIN	4047109082403
Item class	24J

Description
Version:

The following are compatible: No. 268883 BK6425, 268884 BK8425, 268888 P25M and 268888 BK8425.

Note:

Use with matching boring head B301. Suitable indexable inserts W30 left-hand and W30/W57 in neutral version.

Technical description

Pack of insert screws	239653 10IP
Suitable for micro-adjustable drilling head No. 238301	100; 120
ISO code indexable insert	TO. X 1403..
Coarse adjustment travel S	11 mm
External $\varnothing D_1$	32 mm
Reach L_1	97 mm
Type of product	Boring tool

Accessories

Torx Plus® insert screw set 10 pieces Drive 10IP	239653 10IP
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 10IP	674252 10IP
Torque screwdriver, fixed setting set torque 2,8 N·m	211750 2,8