


**KOMET® micro-adjustable drilling head B301, Ø Dmin: 120mm**

**Order data**

Order number	238301 120
GTIN	4047109005761
Item class	24B

**Description**
**Version:**

**With ABS® connection B301 and accepts M302 precision turning cartridge.**

The smallest adjustment is 0.002 mm on the Ø using the vernier. Central coolant supply to the cutting edge.

**Application:**

**For bores from Ø 29.5 to 199 mm.**

For high precision setting, turning cartridge can be adjusted after clamping.

**Note:**

Please order the suitable precision cartridge No. 238310 (M302) and indexable inserts (see group 26) separately.

Through-coolant: yes

Spindle range: 120 - 141 mm

Overhang L<sub>1</sub>: 90 mm

ABS® shank Ø D<sub>s</sub>: 80

Application: 238310 60

Insert screw set: 249900 SW10

**Technical description**

Application	238310 60
Spindle range	120 - 141 mm
ABS® shank Ø D <sub>s</sub>	80

Minimum $\varnothing D_{\min}$	120
Overhang $L_1$	90 mm
Insert screw set	249900 SW10
Shank	ABS
Use for drilling	Cross-drilling
Use for drilling	oblique exit
Use for drilling	oblique spot drilling
Through-coolant	yes
Type of product	Boring tool

---

## Accessories

Set of insert screws DIN 913 10-piece Drive SW10	249900 SW10
KOMET® precision cartridge M302 Type 60	238310 60