



## Li-ion battery cell rechargeable, Type: AA2000



### Order data

Order number	081568 AA2000
GTIN	4013674193974
Item class	08C

### Description

#### Version:

High-quality ANSMANN micro AA lithium battery with safety board for excellent safety and integrated type C charging socket.

The integrated safety board protects against overcharging, overload, short circuits and deep discharge. Easily charge the rechargeable battery using a commercially available type C charging cable. Amongst others, a PC, a power bank or a USB power supply unit (5 V) can be used as the power supply. The rechargeable battery can also be charged with a lithium charger (max. 2.6 A charging current). Charge status LED on the positive terminal. Flashes red when charging. Once the rechargeable battery is fully charged, it lights up steady red. Max. continuous discharge current 0.5 A, energy content 0.74 Wh.

#### Supplied with:

4 pcs. mignon AA Li-ion rechargeable battery type 2000 + 4-in-1 type C cable.

### Technical description

Battery capacity	1800 mAh
rechargeable	yes
Type of rechargeable battery	Mignon, AA

chemical composition	Lithium-ion
Number of rechargeable batteries contained	4
Battery voltage	1.5 V
International size	LR6
Type of product	Cordless