



## Li-ion battery cell rechargeable, Type: AAA500



### Order data

Order number	081568 AAA500
GTIN	4013674193967
Item class	08C

### Description

#### Version:

High-quality ANSMANN micro AAA lithium battery with safety board for excellent safety and integrated type C charging socket. The integrated safety board protects against overcharging, overload, short circuits and deep discharge. Easily charge the rechargeable battery using a commercially available type C charging cable. Amongst others, a PC, a power bank or a USB power supply unit (5 V) can be used as the power supply. The rechargeable battery can also be charged with a lithium charger (max. 2.6 A charging current). Charge status LED on the positive terminal. Flashes red when charging. Once the rechargeable battery is fully charged, it lights up steady red. Max. continuous discharge current 2 A, energy content 3.26 Wh.

#### Supplied with:

4 pcs. micro AAA Li-ion rechargeable battery type 500 + 4-in-1 type C cable.

### Technical description

Battery voltage	1.5 V
rechargeable	yes
chemical composition	Lithium-ion

Type of rechargeable battery	Micro, AAA
Battery capacity	400 mAh
Number of rechargeable batteries contained	4
International size	LR3
Type of product	Cordless