

Garant
GARANT Master Eco SET HB7130-2, right-hand, Shank size: 20mm

Order data

Order number	255162 20
GTIN	4067263134077
Item class	29W

Description
Supplied with:

1 pc. lever lock toolholder No. 250000 and 40 pcs. indexable inserts No. 250158 HB7130-2.

Technical description

suitable indexable insert	CN.. 1204..
Functional width L ₄	25 mm
Overall length L	90 mm
Head length L ₁	30 mm
Standard	Works standard
Standard	DIN ISO 5610
Shank size	20 mm
ISO code toolholder	PCLNR/L 2020X12
Application type	right-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Screw-on toolholder