

Garant
GARANT Master Eco SET HB7130-2, right-hand, Shank size: 25mm

Order data

Order number	265132 25
GTIN	4067263135524
Item class	29W

Description
Supplied with:

1 pc. lever lock toolholder No. 260290 and 40 pcs. indexable inserts No. 260462 HB7130-2.

Technical description

Head length L_1	30 mm
Functional width L_4	32 mm
suitable indexable insert	DC.. 11T3..
Overall length L	100 mm
ISO code toolholder	SDJCR/L 2525H11
Standard	Works standard
Standard	DIN ISO 5610
Shank size	25 mm
Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Screw-on toolholder