

Garant GRIDLINE

Shelf with lashing rods, for compartment width in G: 40



Order data

Order number	998410 40
GTIN	4067263135920
Item class	9GI

Description

Version:

Galvanised shelf of sheet steel with round material at the front and rear for lashing.

Suitable for:

GridLine cabinets depth 20G.

Supplied with:

Shelf with lashing rods.

Technical description

Usable depth	425 mm
Usable width	950 mm
suitable for cabinet width in G	40
suitable for cabinet depth in G	20
Depth	425 mm
Width	950 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Material	Galvanised
Type of product	Storage shelf

