

**HOLEX****Cup brush Steel wire 0.50 mm, Brush Ø D1× thread M: 65XM14mm****Order data**

Order number	GG5721 65XM14
GTIN	4067263136408
Item class	GGN

**Description****Version:**

Smooth steel wire, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Corresponds to No. 572103.

**Application:**

Specially to accept angle grinders.  
With **M14 internal thread.**

**Technical description**

Thread M	M14
Bristle thickness	0.5 mm
Brush Ø D <sub>1</sub>	65 mm
Length of brush section H <sub>1</sub>	20 mm
maximum speed	12500 min <sup>-1</sup>
Safety support ring	no
Brush material	Steel wire
Type of product	Cup brush

---

## Accessories

Cup brushSteel wire 0.50 mm Brush Ø D1× thread M  
65XM14 mm

---

572103 65XM14