

**Value pack cup brush steel wire 0,35 mm****Order data**

|              |               |
|--------------|---------------|
| Order number | GG5730 60     |
| GTIN         | 4067263136156 |
| Item class   | GGN           |

**Description****Version:**

Waved wire firmly crimped into the steel body. For use on angle grinders and on stationary machines.

With **M14 internal thread**.

Corresponds to No. 573005. With **M14 internal thread**.

**Application:**

Very well suited for brushing surfaces, deburring, removing rust, polishing, removing paint, primer, varnish, scale etc.

**Technical description**

|                                        |                         |
|----------------------------------------|-------------------------|
| maximum speed                          | 12000 min <sup>-1</sup> |
| Length of brush section H <sub>1</sub> | 20 mm                   |
| Brush Ø D <sub>1</sub>                 | 65 mm                   |
| Bristle thickness                      | 0.35 mm                 |
| Thread M                               | M14                     |
| Brush material                         | Steel wire              |
| Type of product                        | Cup brush               |

---

## Accessories

Cup brushSteel wire 0.35 mm Brush Ø D1 60 mm

573005 60