

**Dished bevel brush Steel wire 0.50 mm, Brush Ø D1× thread M: 125XM14mm****Order data**

Order number	GG5713 125XM14
GTIN	4067263136521
Item class	GGN

**Description****Version:**

Dished **bevel brush** with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body.  
**Very aggressive brushing effect with high wear resistance.**

Corresponds to No. 571303.

**Application:**

**Left knotted**, reliably avoids premature unwinding.

Ideal for working where access is difficult and for heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

With **internal thread M14**. for direct mounting **on angle grinders**.

**Technical description**

Thread M	M14
maximum speed	12500 min <sup>-1</sup>
Bristle width L <sub>1</sub>	12 mm
Brush material	Steel wire
Twisted knotting	left knotted
Type of product	Bevel brush

---

## Accessories

Dished bevel brushSteel wire 0.50 mm Brush Ø D1× thread  
M 125XM14 mm

---

571303 125XM14