

Garant**Abrasive flap disc long life CER, conical, Ø 125 mm, Grit: 40****Order data**

| | |
|--------------|---------------|
| Order number | GG5225 40 |
| GTIN | 4067263136576 |
| Item class | GGN |

Description**Version:**

- **High-quality self-sharpening ceramic grit (CER) for maximum abrasive power and low contact pressure.**
- **Active coating for cool cutting.**
- **Sturdy poly-cotton mixed fabric for ideal wear characteristics and stability, even when used on edges.**
- **Ergonomic and vibration-damping polyester plastic backing pad (can be reset).**
- **Best results on high-power angle grinders.**

long life - very closely spaced flap strips, for **maximum tool life**.

Corresponds to 565225.

Application:

General purpose abrasive disc operations, surface abrasion, material removal and edge smoothing.

Technical description

| | |
|-------------------|----------|
| Grit | 40 |
| Bore Ø | 22.23 mm |
| Shape description | dished |

| | |
|---|--------------------|
| Contents | 100 |
| Disc Ø | 125 mm |
| Grinding media | Ceramic grit (CER) |
| Grinding medium code | Ceramic |
| abrasive, cooling coating | yes |
| Iron, sulphur and chlorine constituents | < 0,1 % |
| Product name attribute | Ø 125 mm |
| optimised for material | INOX |
| maximum circumferential speed | 80 m/s |
| Type of product | Abrasive flap disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable only under restricted conditions | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |
| CuZn | suitable only under restricted conditions | | |
| Uni | suitable | | |
| dry | suitable | | |

Accessories

Abrasive flap disclong life CER, conical Grit 40

565225 40