

**Garant****Cutting disc, stainless steel EXTRA THIN, Disc Ø / quantity: 125/200****Order data**

|              |                |
|--------------|----------------|
| Order number | GG5272 125/200 |
| GTIN         | 4067263136965  |
| Item class   | GGN            |

**Description****Version:**Special type for **stainless steel**.New **high-performance version** using state of the art technology with significant productivity advantages and excellent cutting qualities. **Increased cutting performance** due to rough free-grinding side faces; **improved service life**.The thinness of the disc allows **very quick** cutting **with low force and optimum time saving**.**Clean cut edges, virtually no burrs.** Corresponds to No. 563272.**Specification:****A60R-BF.****Technical description**

|                          |          |
|--------------------------|----------|
| Bore Ø                   | 22.23 mm |
| for material thicknesses | 3 - 5 mm |
| Shape description        | straight |
| Disc Ø                   | 125 mm   |
| Contents                 | 200      |
| Disc thickness           | 1 mm     |

|   |                |
|---|----------------|
| Specification                           | A60R-BF        |
| Grinding medium code                    | A              |
| Iron, sulphur and chlorine constituents | < 0.1 %        |
| recommended approach angle              | Radius degrees |
| optimised for material                  | INOX           |
| Propulsive equipment                    | Angle grinder  |
| maximum circumferential speed           | 80 m/s         |
| Type of product                         | Cutting disc   |

### User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable only under restricted conditions |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| Steel < 67 HRC                 | suitable                                  |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable                                  |                |          |
| GG(G)                          | suitable only under restricted conditions |                |          |
| CuZn                           | suitable only under restricted conditions |                |          |
| Plastic, GRP                   | suitable only under restricted conditions |                |          |
| Uni                            | suitable only under restricted conditions |                |          |
| dry                            | suitable                                  |                |          |

## Accessories

Cutting disc, high-performance version EXTRA THIN,  
STAINLESS STEEL Disc Ø 125 mm

---

563272 125