

**Garant**
**Nut lock 2GP43, Contents: 50ml**

**Order data**

Order number	GG8061 50
GTIN	4067263137207
Item class	00N

**Description**
**Version:**

The use of thread-lockers prevents the screw fastenings from accidentally releasing and coming undone. The single-component anaerobic thread-lockers are suitable for all thread types and forms. Screw fastenings are sealed. Seizing is reliably prevented.

Type **2GP43** medium-strength. Seals and locks many types of screw fastenings. High resistance to vibrations. Quick curing on a high number of ferrous metals. Increased oil tolerance.

**Feature:**

Contents: 3 pieces

**Application:**

**Low strength** – Can be undone with normal tools. **Medium strength** – Can be undone with normal tools. **High strength** – Can be undone only with special tools or by heating (>150°C).

**Note:**

Clean the material to be worked on in advance with cleaner without hazard labels No. 088004.

**Technical description**

Working life after date of manufacture	24 mo
Series	GreenPlus

Colour	blue
Disassembly	with normal tool
Suitable for material	Metal
Flashpoint	100 °C
Density	1.08 g/cm <sup>3</sup>
minimum break-away torque	15 - 25 Nm
Storage temperature	5 - 23 °C
Shape	liquid
Touch dry after	5 - 15 min
Chemical basis	Methacrylate
Strength class	medium strength
Functional strength to	3 - 6 h
Suitable for application area	general purpose use
Suitable for application area	oily surfaces
Suitable for application area	Thread sealing
for thread size M to	M36
Operating temperature range	-55 - 180 °C
Characteristics	vibration-resistant
Characteristics	sealing
Characteristics	fluorescent under UV light
Capacity	50 ml
Sustainability	GARANT GreenPlus
Dynamic viscosity	1500 - 4000 mPas
Type of product	Nut lock

## Accessories

Thread locking2GP43 Contents 50 ml

088061 50