

Garant**Thread sealant 5GP77, Contents: 50ml****Order data**

Order number	GG8066 50
GTIN	4067263136477
Item class	00N

Description**Version:**

Thread sealants prevent leakage of gaseous and liquid media. Thread sealants are typically used for sealing conical metal threads and connecting pieces, amongst other things.

Type **5GP77**. Seals conical/cylindrical pipe thread fastenings up to R3 inch, e.g. gas piping systems. Heat-resistant.

Feature:

Contents: 3 pieces

Note:

Clean the material to be worked on in advance with cleaner without hazard labels No. 088004.

Technical description

Colour	yellow
Disassembly	with normal tool
Density	1.09 g/cm ³
Operating temperature range	-55 - 180 °C

Sustainability	GARANT GreenPlus
Maximum gap size	0.35 mm
Series	GreenPlus
Dynamic viscosity	20000 - 40000 mPas
Functional strength to	3 - 6 h
Suitable for material	Metal
Suitable for application area	Pipe sealant
Suitable for application area	Pipe threads
minimum break-away torque	20 - 30 Nm
Chemical basis	Methacrylate ester
Capacity	50 ml
for imperial thread size	3 in
Strength class	high-strength
Touch dry after	5 - 15 min
for thread size M to	M80
Storage temperature	5 - 23 °C
Working life after date of manufacture	24 mo
Shape	liquid
Flashpoint	100 °C
Characteristics	fluorescent under UV light
Characteristics	labelling-free
Type of product	Sealant

Accessories

Thread sealant5GP77 Contents 50 ml

088066 50