

**Garant****Thread sealant 5GP42, Contents: 50ml****Order data**

Order number	GG8064 50
GTIN	4067263136453
Item class	00N

**Description****Version:**

Thread sealants prevent leakage of gaseous and liquid media. Thread sealants are typically used for sealing conical metal threads and connecting pieces, amongst other things.

Type **5GP42**. Sealant for workpieces with threads in hydraulic or pneumatic systems and connecting parts. Effective protection against oil, water, hydrocarbons and chemical products.

**Feature:**

Contents: 3 pieces

**Note:**

Clean the material to be worked on in advance with cleaner without hazard labels No. 088004.

**Technical description**

Sustainability	GARANT GreenPlus
Maximum gap size	0.15 mm
minimum break-away torque	15 - 25 Nm
Touch dry after	10 - 20 min

for imperial thread size	3/4 in
Strength class	medium strength
Operating temperature range	-55 - 180 °C
Dynamic viscosity	400 - 800 mPas
for thread size M to	M26
Suitable for material	Metal
Shape	liquid
Characteristics	fluorescent under UV light
Density	1.08 g/cm <sup>3</sup>
Series	GreenPlus
Disassembly	with normal tool
Colour	brown
Capacity	50 ml
Chemical basis	Methacrylate ester
Flashpoint	100 °C
Functional strength to	3 - 6 h
Working life after date of manufacture	24 mo
Storage temperature	5 - 23 °C
Type of product	Sealant

## Accessories

Thread sealant5GP42 Contents 50 ml

088064 50