

Garant

Flat gasket sealants 5GP74, Contents: 50ml



Order data

Order number	GG8067 50
GTIN	4067263136484
Item class	00N

Description

Version:

Sealant that cures when applied as a hermetic seal between close-fitting metal surfaces. Type **5GP74**. For sealing flanges and surfaces. Quick-curing, slightly flexible sealant film.

Feature:

Contents: 3 pieces

Note:

Clean the material to be worked on in advance with cleaner without hazard labels No. 088004.

Technical description

Touch dry after	5 - 20 min
Maximum gap size	0.25 mm
Disassembly	with normal tool
Flashpoint	100 °C
Suitable for application area	Flange connection
Suitable for application area	Liquid gasketing

Operating temperature range	-55 - 180 °C
Storage temperature	5 - 23 °C
Strength class	medium strength
Working life after date of manufacture	24 mo
Capacity	50 ml
Density	1.09 g/cm ³
Shape	liquid
Dynamic viscosity	23000 - 35000 mPas
Characteristics	water-resistant
Characteristics	fluorescent under UV light
Chemical basis	anaerobic methacrylate
Colour	orange
Suitable for material	Metal
Sustainability	GARANT GreenPlus
Series	GreenPlus
Functional strength to	3 - 6 h
minimum break-away torque	10 - 20 Nm
Type of product	Sealant

Accessories

Flat gasket sealant5GP74 Contents 50 ml

088067 50